#### Product Features:

ahg shooting glasses CLASSIC

The ahg shooting glasses have a fine adjustment by knurled nut for easy adjustment of the lens frame and eye shield to the right or left.

The nose bridge and the eye shield can be adjusted in height by knurled screw. The ear bows are equipped with a spring hinge to improve the wearing comfort.

Product Parameters:

Lens holder size: Ø24mm, Ø37mm & Ø42mm

Product Size: 156mm×150mm

Packing Size: 190mm×165mm×50mm

Weight: 38g

#### Warnings and Cautions:

Do not puncture, throw, drop, bend, disassemble, or attempt to repair the product.

Keep your SC-8900 dry and away from moisture and corrosive materials. Do not wash your SC-8900 with chemicals or soaps. Instead wipe the top and bottom with a soft, water dampened cloth. Wipe the inputs and outputs with gently with a soft dry cloth.

Do not expose the unit to fire or excessive heat. Never throw away electronic devices in the garbage. Recycle according to local recycling and environment regulations.

 Item No.: 8900-24
 (Shooting Glasses, with lens frame 24 mm, with eyeshade and case)

 Item No.: 8900-37
 (Shooting Glasses, with lens frame 37 mm, with eyeshade and case)

 Item No.: 8900-42
 (Shooting Glasses, with lens frame 42 mm, with eyeshade and case)

 Item No.: 8910-24
 (Lens frame 24 mm)

 Item No.: 8910-37
 (Lens frame 37 mm)

 Item No.: 8910-42
 (Lens frame 42 mm)

 Item No.: 8912
 (Eye blinder)

| Item No.: 8914-24 | (Movable Iris for lens frame 24 mm) | Item No.: 8914-37 | (Movable Iris for lens frame 37 mm) | Item No.: 8914-42 | (Movable Iris for lens frame 42 mm) |

# SHOOTING FRAME MANUAL

S - C - 8 9 0 0

# ahg-Anschütz Handels GmbH


Fon +49 - (0)731 - 420 31 Fax +49 - (0)731 - 420 33 www.ahg-anschuetz.de
info@ahg-anschuetz.de

www.facebook.com/ahg.anschuetz shop.ahq-anschuetz.de




SC - 8900 Shooting Frame

MANUAL(English)



Thank you for purchasing the SC-8900 Shooting Frame. Before using this product, please read these instructions carefully to learn about the features and capabilities of the Shooting frame and how you can get the best out of it.

- 1)Adjustable control
- ②Hand screw
- 3 Hand nut
- 4 Lens holder
- ⑤Rod
- **6**Hand screw
- 7 Nose rod
- **®**Hand screw
- 10 Socket set screw



# 1, Adjust the relative position of lens holder and pupil

To rotate the Hand nut ③, and to drive Adjustable control ① to move in the beam, so, it make the user's pupil with Lens londer ④ in the right position. The same to the Eye-blinder ④.



## 2, Adjust up and down position

To rotate the Hand screw 2, and to move Rod 5 up and down.




## 3, Adjust the nose rod height

To rotate the Hand screw 6, and to move Nose Rod 7 up and down.




## 4, Adjust the Eye-blinder height

To rotate the Hand screw<sup>®</sup>, and to move Eye-blinder <sup>®</sup> up and down.



### 5, Adjust the Lens holder direction

To loose Socket set screw (11), and to changd the Lens holder (5) direction,



### 6, Adjust the Lens holder angle

To loose Socket set screw ①, and to adjust the Lens holder angle.



#### Limited 1-Year Warranty:

It warrants that its SC-8900 Shooting Frame, and the component parts thereof, will be free of defects in workmanship and materials for a period of one year from the date of first consumer purchase. This warranty may be enforced by the first consumer purchaser.

It will, without charge, repair or replace, at its option, defective Shooting Frame, products or component parts upon delivery to the Service Department accompanied by proof of the date of first consumer purchase, such as a duplicated copy of a sales receipt. You must pay any initial shipping charges required to ship the product for warranty service, but the return charges will be at a dy's expense, if the product is repaired, this warranty gives you specific rights.

#### Exclusions: This limited warranty does not apply:

- 1. To any product damaged by accident.
- In the event of misuse or abuse of the product, or as a result of unauthorized alterations or repairs.
- 3. If the serial number has been altered, defaced or removed. All implied warranties, including warranties of merchantability and fitness for a particular purpose are limited in duration to the length of this warranty.

It shall not be liable for any incidental, consequential or other damages; including, without limitation, damages resulting from loss of use or cost of installation

Some states do not allow limitations on how long an implied warranty lasts and/or do not allow the exclusion of incidental or consequential damages, so the above limitations may not apply to you.